SATMAGAN 135

A fast, accurate and reliable instrument for measuring the magnetite content in samples.

Accurate Measurement of Magnetic Material

Instant Analysis

Reliable

Cost Effective

Accurate measurement of ferrous material content in iron ore is extremely difficult and time-consuming by conventional chemical methods in the laboratory. This is overcome by measuring the total magnetic moment of the sample in a high magnetic field thereby measuring the magnetite content in the sample accurately, reliably and faster than measurement based on susceptibility of the material.

For over 40 years Satmagan has been in use in the mining industry around the world and has been proven to be a fast, accurate and reliable instrument for measuring the magnetite content in samples. With a measuring time of roughly one minute and an accuracy of 0.4 % or less Satmagan is considered to be an ideal instrument for securing an optimal return on investment.

The principle behind the Satmagan 135 is to measure the force acting on the sample in a magnetic field with a spatial gradient. The magnetic field is strong enough to saturate the magnetic component in a sample. A Satmagan can be used to measure any sample with only one magnetic component. Alternatively, it can measure a component with a dominant concentration and/or dominant specific magnetic moment.

Once Satmagan is calibrated it is easy and fast to use. Therefore it is an ideal instrument for analyzing mixtures of magnetic and non-magnetic components.

Other Industrial and Mining Products

Metcorr 117C metal detector for mines, quarries, recycling plants and other industrial facilities.

About Rapiscan Systems

Rapiscan Systems designs, manufactures and markets security and inspection systems worldwide. The company is a wholly-owned subsidiary of a Nasdaq-listed OSI Systems, Inc. and headquartered in Hawthorne, California. It has additional offices and manufacturing in Canada, Finland, India, Malaysia, Singapore, United Kingdom and the United States. For more information on Rapiscan Systems, please visit www.rapiscansystems.com.





Features

Maximum Error 0.4% Of The Measurement Range (The Result Can Be As Good As 0.1%)

Analysis Time Roughly One Minute

Powder, Granular Or Solid Samples Used For The Measurement

Stabilized For Voltage And Temperature

Applications

The Satmagan was designed especially to measure magnetite in iron ore concentrations. It can be used in various applications:

Analysis of magnetite in iron ores, concentrates and tailings

Control of copper and nickel smelting by analyzing magnetite and other ferromagnetic oxides in slag

Determination of martensite or ferrite in austenitic steels

Determination retained austenite in steels

Control of magnetizing roasting

Control of oxidizing roasting of carbonate ores

Controlling the heat hardening of pellets

Control of iron ore sintering



www.rapiscansystems.com

www.iacsa.com.mx | Tel: 01 (81) 81 91 07 54 / 56 | cotizaciones@iacsa.com.mx

SATMAGAN 135

Technical Data	
Materials for Analyses	Magnetite and magnetic iron can be analyzed. The sample can contain only one magnetic component, or have one component with a dominant concentration and/or specific magnetic moment.
Type of Sample	powder, granular or solid samples maximum volume of sample 1.2 cu cm (0.073 cu inch) recommended sample size: sample container filled up grain size: An average grain size greater than 150um (100 mesh) does not disturb the measurements. For finer materials, the Satmagan gives slightly lower readings, so a different calibration curve is required.
The Range of Measurement	Fine Range: 0 to 100 % by magnetite weight Course Range: 0 to 200 % by magnetite weight for stronger magnetic materials
Reproducibility	0.2% by weight
Sample Containers	An acrylic container has a sample volume of 1.2 cu cm (0.073 cu inch). Its plug is made of polyethylene. Average weight: container 1010mg, plug 543mg. The weight distribution of sample containers is approx. +/- 5mg, corresponding to an error +/- 0.12% in a 4g sample. The weight distribution of plugs is approx. +/- 1mg, corresponding to an error of +/- 0.08% in a 4g sample.
Operating Temperature Range	+10°C to +40°C (+50°F to +100°F)
Ambient Humidity	Up to 95% relative
Controls	power switch range switches sample weight balancing knob crank for turning magnet sample magnetic control knob
Line Voltage	210240V or 110130V (to be specified when ordering)
Line Frequency	50 to 60Hz
Power Consumption	10W
Physical Specifications	
Overall Dimensions	length 64 cm (26 in.), width 34 cm (13.5 in.), height 37 cm (15 in.), weight 63 kg(145 lbs.) net.
Export Package	length 95 cm (38 in.), width 57 cm (22 in.), height 57 cm (22in.), weight 95 kg (210 lbs.) gross
CE Compliance	Yes



Satmagan 135 front view



Satmagan 135 rear view

With continual development of our products Rapiscan Systems reserves the right to amend specifications without notice. Product pictures are for general reference. Please note that due to US laws and regulations, not all Rapiscan products are available for sale in all countries without restriction. Please contact your Rapiscan Systems sales representative for more information.



ONE COMPANY - TOTAL SECURITY

SALES OFFICE Rapiscan Systems 16 Rocklea Drive Port Melbourne, Victoria, 3207 AUSTRALIA Tel: +61 3 9929 4600 Fax: +61 3 9929 4655

EMAIL industrial@rapiscansystems.com

www.rapiscansystems.com



cotizaciones@iacsa.com.mx Ph +52 (81) 81 91 07 54 /56



Rapiscan Systems is ISO 9001:2008 Certified